



EAL

ERGOSTYLE ADJUSTABLE HANDLES



Original ELES Model ERX.



Type	Handle	Locking Element	Push Button	Threaded Insert	Stud
EAL	Glass-fiber reinforced polyamide plastic	Glass-fiber reinforced polyamide plastic	Polyamide plastic Glossy Finish	Brass (C3604B)	Steel(S10C) Zinc plated finish
EAL-SUS	Black matte	Black	Orange	Stainless steel(SUS303)	Stainless steel(SUS303)

Size	No. of Teeth	R	H	D	H1	H2	M	D1	H3	A	S
EAL EAL-SUS	30B	18	30	15.5	29.5	33.5	M 4×0.7	12	23	9	6
	30						M 5×0.8				
	30A						M 6×1				
	44						M 5×0.8				
	44A	44	32.5			36	M 6×1		25	11	
	63	20	63	43	37.5	47	M 8×1.25	15	34.5	13.5	8
	63A										
	78B	24	78	54	47	58	M10×1.5	19	44	16	12
	78A										
	95	26	95	64.5	26.5	54.5	M12×1.75	21.5	53	18	13

Tapped

Brass			Stainless Steel		
Part Number	Lf	Weight(g)	Part Number	Lf	Weight(g)
EAL30B	10	8	-	-	-
EAL30		7	EAL30 -SUS	6	8
EAL30A		6	EAL30A-SUS	10	6
EAL44		10	EAL44 -SUS	6	11
EAL44A	16	21	EAL44A-SUS	10	10
EAL63			EAL63 -SUS	12	22
EAL63A	13	20	EAL63A-SUS	13	20
EAL78B	20	46	EAL78B-SUS		46
EAL78	18	44	EAL78 -SUS	17	44
EAL78A	17	43	-	-	-
EAL95	20	51	EAL95 -SUS	20	52

Stud

Steel			Stainless Steel		
Part Number	L	Weight(g)	Part Number	L	Weight(g)
EAL30 ×10	10	6	EAL30 ×10-SUS	10	6
EAL30 ×16	16		EAL30 ×16-SUS	16	7
EAL30 ×20	20	7	-	-	-
EAL30A×10	10	8	EAL30A×10-SUS	10	8
EAL30A×16	16	9	EAL30A×16-SUS	16	9
EAL30A×20	20	10	EAL30A×20-SUS	20	10
EAL30A×25	25	11	EAL30A×25-SUS	25	11
EAL30A×30	30	12	EAL30A×30-SUS	30	12
EAL30A×40	40	14	-	-	-
EAL44 ×10	10	11	EAL44 ×10-SUS	10	10
EAL44 ×16	16	12	EAL44 ×16-SUS	16	12
EAL44 ×20	20	13	-	-	-
EAL44A×10	10	13	EAL44A×10-SUS	10	13
EAL44A×16	16	14	EAL44A×16-SUS	16	14
EAL44A×20	20	15	EAL44A×20-SUS	20	16
EAL44A×25	25	16	EAL44A×25-SUS	25	17
EAL44A×30	30	17	EAL44A×30-SUS	30	18
EAL44A×40	40	19	-	-	-
EAL63 ×16	16	29	-	-	-
EAL63 ×20	20	30	EAL63 ×20-SUS	20	31
EAL63 ×30	30	32	EAL63 ×30-SUS	30	32
EAL63 ×40	40	32	EAL63 ×40-SUS	40	33
EAL63A×16	16	32	EAL63A×16-SUS	16	31
EAL63A×20	20	32	EAL63A×20-SUS	20	32
EAL63A×25	25	34	EAL63A×25-SUS	25	33
EAL63A×30	30	36	EAL63A×30-SUS	30	36
EAL63A×35	35	38	-	-	-
EAL63A×40	40	40	EAL63A×40-SUS	40	41
EAL63A×50	50	43	EAL63A×50-SUS	50	44
EAL63A×60	60	46	EAL63A×60-SUS	60	47
EAL78 ×20	20	58	EAL78 ×20-SUS	20	58
EAL78 ×25	25	61	-	-	-
EAL78 ×30	30	64	EAL78 ×30-SUS	30	64
EAL78 ×40	40	70	EAL78 ×40-SUS	40	67
EAL78 ×50	50	76	EAL78 ×50-SUS	50	68
EAL78 ×60	60	82	EAL78 ×60-SUS	60	70
EAL78A×25	25	71	-	-	-
EAL78A×30	30	74	EAL78A×30-SUS	30	74
EAL78A×50	50	78	EAL78A×50-SUS	50	79
EAL95 ×30	30	86	EAL95 ×30-SUS	30	87
EAL95 ×50	50	90	EAL95 ×50-SUS	50	93

Installation Instructions



Lift the handle to disengage the teeth from the locking element.



Turn the lifted handle to a desired position.



When the handle is released, the return spring automatically engages the teeth again for further tightening.

Features:

Ergonomic design for comfortable gripping
Knurled hub for easier initial tightening
Push button is available in black, gray, yellow, light blue, or red on request.

Caution :

Use in hot or highly humid circumstances can deteriorate the plastic material

Technical Information

Working temperature : Between -30°C and 130°C